## Quadrathane™ ARC-72D

Aroma

Thermoplastic Polyurethane Elastomer (PC Based)

Biomerics, LLC

General Information

Features

## Message:

Quadrathane™ ARC-72D is high performance aromatic polycarbonate thermoplastic polyurethane. The polymer is naturally clear and supplied in small pellets for ease of processing. The material exhibits excellent mechanical properties, oxidative stability, biocompatibility, superior biostability in long term implantable devices, high resiliency, and chemical resistance. The resin has consistent melt flow properties making it ideal for extrusion. Quadrathane™, Quadraflex™, Quadraban™ and Quadraplast™ performance polymers are primarily used in life science and medical applications including vascular access devices, surgical supplies, respiratory devices, tracheotomy devices, and other medical applications. Typical end products include tubing, catheter parts, balloons, and various medical device components. These performance polymers are available in a variety of durometers, radiopacifiers, colors, and custom formulations.

Features	Aroma							
	Antioxidation							
	Workability, good  Good liquidity  Good chemical resistance  Biocompatibility							
					Elastic			
					Uses	Pipe fittings		
	Human implant							
Surgical instruments								
Medical/nursing supplies								
Appearance	Clear/transparent							
Forms	Particle							
Processing Method	Extrusion							
	Injection molding							
Physical	Nominal Value	Unit	Test Method					
Specific Gravity	1.18	g/cm³	ASTM D792					
Melt Mass-Flow Rate (MFR) (190°C/2.16 kg)	6.0	g/10 min	ASTM D1238					
Molding Shrinkage - Flow	0.80 - 1.0	%	ASTM D955					
Hardness	Nominal Value	Unit	Test Method					
Durometer Hardness (Shore D)	72		ASTM D2240					
Mechanical	Nominal Value	Unit	Test Method					
Flexural Modulus	552	MPa	ASTM D790					
Elastomers	Nominal Value	Unit	Test Method					
Tensile Stress (10% Strain)	17.6	MPa	ASTM D412					

Tensile Stress			ASTM D412
100% strain	24.6	MPa	ASTM D412
300% strain	31.7	MPa	ASTM D412
Tensile Strength (Break)	58.6	MPa	ASTM D412
Tensile Elongation (Break)	350	%	ASTM D412
Thermoset	Nominal Value	Unit	
Post Cure Time (38°C)	6.0 - 10	hr	
Injection	Nominal Value	Unit	
Drying Temperature	54.4	°C	
Drying Time	4.0	hr	
Suggested Max Moisture	< 3.0E-3	%	
Rear Temperature	177	°C	
Front Temperature	191	°C	
Nozzle Temperature	196	°C	
Processing (Melt) Temp	204	°C	
Mold Temperature	4.44 - 32.2	°C	
Injection Rate	Slow		
Screw Compression Ratio	2.5:1.0 - 3.5:1.0		
Injection instructions			
Injection Speed: 10 g/secCooling/Hol	d TIme: Long, at least 50% of cycle (	20 to 60 secs depending on thickn	ess)
Extrusion	Nominal Value	Unit	
Drying Temperature	54.4	°C	
Drying Time	4.0	hr	
Suggested Max Moisture	< 0.030	%	
Cylinder Zone 1 Temp.	171	°C	
Cylinder Zone 2 Temp.	182	°C	
Cylinder Zone 3 Temp.	188	°C	
Cylinder Zone 4 Temp.	193	°C	
Melt Temperature	193	°C	
Die Temperature	193 - 216	°C	
Dools Drossums	6.00 12.4	MD-	

Screen Pack: 250 meshScrew Speed: Low sheer, 150 to 250 rpmWater Bath: 80 to 110°F

6.89 - 12.4

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

MPa

## Recommended distributors for this material

## Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519 Phone: +86 13424755533 Email: sales@su-jiao.com

**Back Pressure** 

Extrusion instructions

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

