

RTP 1400 AG-320

Polyethersulfone

RTP Company

Message:

Glass Fiber

General Information			
Filler / Reinforcement	Glass fiber reinforced material, 20% filler by weight		
RoHS Compliance	Contact manufacturer		
Processing Method	Injection molding		
Physical	Nominal Value	Unit	Test Method
Specific Gravity	1.51	g/cm ³	ASTM D792
Molding Shrinkage - Flow (3.20 mm)	0.20	%	ASTM D955
Water Absorption (23°C, 24 hr)	0.40	%	ASTM D570
Moisture Content	0.040	%	
Primary Additive	20	%	
Mechanical	Nominal Value	Unit	Test Method
Tensile Modulus	5520	MPa	ASTM D638
Tensile Strength	105	MPa	ASTM D638
Tensile Elongation (Yield)	2.0 - 4.0	%	ASTM D638
Flexural Modulus	5520	MPa	ASTM D790
Flexural Strength	169	MPa	ASTM D790
Impact	Nominal Value	Unit	Test Method
Notched Izod Impact (3.20 mm)	48	J/m	ASTM D256
Unnotched Izod Impact (3.20 mm)	670	J/m	ASTM D4812
Thermal	Nominal Value	Unit	Test Method
Deflection Temperature Under Load			ASTM D648
0.45 MPa, not annealed	210	°C	ASTM D648
1.8 MPa, not annealed	209	°C	ASTM D648
Electrical	Nominal Value	Unit	Test Method
Volume Resistivity	> 1.0E+12	ohms · cm	ASTM D257
Flammability	Nominal Value	Unit	Test Method
Flame Rating (1.50 mm, ** Values per RTP Company testing.)	V-0		UL 94
Injection	Nominal Value	Unit	
Drying Temperature	149	°C	
Drying Time	6.0	hr	
Dew Point	-31.7	°C	
Processing (Melt) Temp	343 - 377	°C	
Mold Temperature	135 - 177	°C	

Injection Pressure	68.9 - 103	MPa
Injection instructions		

Desiccant Type Dryer Required.

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533

Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China



WECHAT