THERMOLAST® K TC8HFZ (Series: UV/HF/SF)

Thermoplastic Elastomer

KRAIBURG TPE

Message:

The UV/HF/SF Series is your material solution for applications requiring high UV resistance, perfect surface finish and high flow ability. It is particularly appropriate for automotive exterior components.

Typical applications

Cowls gaskets

Roof rims

Water deflectors

Window encapsulations

Material advantages

Easy flowing

Excellent processing behavior

Perfect adhesion to PP

Perfect surface finish

Tested according PV3930 for outdoor use

General Information				
Features	Good UV resistance			
	Workability, good			
	High liquidity			
	Excellent appearance			
Uses	Washer			
	Application in Automobile Field			
	Automotive exterior parts			
Appearance	Black			
Processing Method	Injection molding			
Physical	Nominal Value	Unit	Test Method	
Density	1.02	g/cm³	ISO 1183	
Spiral Flow	85.0	cm		
Hardness	Nominal Value	Unit	Test Method	
Durometer Hardness (Shore A)	77		ISO 7619	
Elastomers	Nominal Value	Unit	Test Method	
Tensile Stress ¹ (Break)	5.00	MPa	ISO 37	
Tensile Elongation ² (Break)	500	%	ISO 37	
Tear Strength ³	19	kN/m	ISO 34-1	
Injection	Nominal Value	Unit		
Drying Temperature	60 - 80	°C		
Drying Time	2.0 - 4.0	hr		
Rear Temperature	180	°C		
Middle Temperature	200	°C		

Front Temperature 220 °C Mold Temperature 25 - 40 °C Injection Pressure 20.0 - 100 MPa Back Pressure 2.00 - 10.0 MPa NOTE Type S2, 200 mm/min 2. Type S2, 200 mm/min Method B, right-angle specimen (cut) Method B, right-angle specimen				
Injection Pressure	Front Temperature	220	°C	
Back Pressure 2.00 - 10.0 MPa NOTE 1. Type S2, 200 mm/min 2. Type S2, 200 mm/min Method B, right-angle specimen	Mold Temperature	25 - 40	°C	
NOTE 1. Type S2, 200 mm/min 2. Type S2, 200 mm/min Method B, right-angle specimen	Injection Pressure	20.0 - 100	MPa	
1. Type S2, 200 mm/min 2. Type S2, 200 mm/min Method B, right-angle specimen	Back Pressure	2.00 - 10.0	MPa	
2. Type S2, 200 mm/min Method B, right-angle specimen	NOTE			
Method B, right-angle specimen	1.	Type S2, 200 mm/min		
	2.	Type S2, 200 mm/min		
3. (cut)		Method B, right-angle specimen		
	3.	(cut)		

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection. All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519

Phone: +86 13424755533 Email: sales@su-jiao.com

No. 215, Lianhe North Road, Fengxian District, Shanghai, China

