

LUVOCOM® 1/GF/30/TF/15/HS/BK

Polyamide 66
Lehmann & Voss & Co.

Message:

LUVOCOM® 1/GF/30/TF/15/HS/BK is a polyamide 66 (nylon 66) material, which contains a 30% glass fiber reinforced material. This product is available in North America, Africa and the Middle East, Latin America, Europe or Asia Pacific.

LUVOCOM®The main characteristics of 1/GF/30/TF/15/HS/BK are:

- anti-warping
- Good stiffness
- Wear-resistant
- heat stabilizer
- Lubrication

Typical application areas include:

- textile/fiber
- engineering/industrial accessories
- Automotive Industry
- business/office supplies

General Information			
Filler / Reinforcement	Glass fiber reinforced material, 30% filler by weight		
Additive	PTFE lubricant (15%) heat stabilizer		
Features	Low friction coefficient Low warpage Rigid, good Good strength Good wear resistance Thermal Stability Lubrication		
Uses	Textile applications Engineering accessories Application in Automobile Field Business equipment		
Appearance	Black		
Physical	Nominal Value	Unit	Test Method
Density	1.51	g/cm³	ISO 1183
Molding Shrinkage	0.20 - 0.50	%	DIN 16901
Water Absorption (23°C, 24 hr)	< 1.0	%	
Mechanical	Nominal Value	Unit	Test Method
Tensile Modulus	10000	MPa	ISO 527-2
Tensile Stress (Break)	160	MPa	ISO 527-2

Tensile Strain (Yield)	3.0	%	ISO 527-2
Flexural Modulus	8000	MPa	ISO 178
Flexural Stress	235	MPa	ISO 178
Coefficient of Friction			
Dynamic	0.24		
Static	0.18		
Flexural Strain at Flexural Strength	3.5	%	ISO 178
Maximum operating temperature-Short Term	160	°C	
Insulation Resistance	> 1.0E+12	ohms	IEC 60167
Thermal	Nominal Value	Unit	Test Method
Continuous Use Temperature	120	°C	UL 746B
Vicat Softening Temperature	250	°C	ISO 306/A
Injection	Nominal Value	Unit	
Drying Temperature			
Hot air dryer, A	75.0	°C	
Vacuum dryer, B	105	°C	
Drying Time			
Hot air dryer, A	6.0 - 16	hr	
Vacuum dryer, B	4.0 - 6.0	hr	
Suggested Max Moisture	0.10	%	
Rear Temperature	290 - 310	°C	
Middle Temperature	290 - 310	°C	
Front Temperature	290 - 310	°C	
Nozzle Temperature	280 - 300	°C	
Processing (Melt) Temp	290	°C	
Mold Temperature	90.0 - 120	°C	
Injection instructions			

General

In general LUVOCOM® can be processed on conventional injection moulding machines while observing the usual technical guidelines.

Any added fibrous materials or fillers may have an abrasive effect. In this case the cylinder and screw should be protected against wear as is usual in the processing of reinforced thermoplastic materials.

Lengthy dwell times for the melts in the cylinder should be avoided.

Lower the temperatures during interruptions!

Predrying (optional)

It is advisable to predry the granulate with a suitable dryer immediately before processing.

The granulate may absorb moisture from the air.

Delivery Form & Storage

Unless indicated otherwise, the material is delivered as 3mm-long pellets in sealed bags on pallets.

Preferably storage should be effected in dry and normally temperatured rooms

Additional Information

During processing the moisture level should not exceed 0.1%, otherwise molecular degradation and surface defects (e.g. smearing) may occur. Due to rapid absorption of water, originally sealed containers should only be opened immediately prior to processing. Excessively high predrying temperatures may cause discoloration.

The processing notes provided merely represent a recommendation for general use. Due to the large variety of machines, geometries and volumes of parts, etc., it may be necessary to employ different settings according to the specific application.

Please contact us for further information.

The information and data on this page are provided by manufacturers and document providers. SHANGHAI SUSHENG assumes no legal liability. It is strongly recommended to verify all technical data with material suppliers before final material selection.All rights belong to the original authors. If any infringement occurs, please contact us immediately.

Recommended distributors for this material

Susheng Import & Export Trading Co.,Ltd.

Tel: +86 21 5895 8519
Phone: +86 13424755533
Email: sales@su-jiao.com
No. 215, Lianhe North Road, Fengxian District, Shanghai, China

